



CHEMEX

Brewing Methods by OCW

Chemex - 6 cup

The Chemex Coffeemaker is a manual, pour-over style glass-container coffeemaker. Designed to be used together with Chemex-Bonded coffee filters, it makes a clear and flavourful coffee without bitterness and sediment.

What to do

- 1** Fold and place the filter into the Chemex. Carefully rinse the paper filter with plenty of hot water. This will remove the paper taste from the filter and preheat the Chemex. Pour away the water.
- 2** Place 45g of medium grind coffee into the Chemex. Ensure you dose the coffee evenly so the coffee bed is flat.
- 3** Pour around 50-100ml of water over the coffee and wait 30 seconds to allow it to bloom.
- 4** Pour 650ml of water in a slow steady pace using a circular motion rotating from the middle out towards the sides of the Chemex. Take care to keep a constant water level in the filter.
- 5** Remove paper and grind from Chemex and serve.